



The Quadtro® Push Connect Washing Machine Outlet Box

THE SINGULAR SOLUTION!

QuadTRO® NOW WITH PUSH CONNECT!

The Quadtro offers one design for every installation





US Patent #6,155,286

When you need a washing machine outlet box, think Quadtro.

The Quadtro Push Connect washing machine outlet box is the ultimate solution for installation flexibility. The Push Connect system makes joining copper, CVPC or PEX pipe simple and fast, without soldering, crimping, or solvent welding! Simply insert the pipe into the valve, and it instantly locks to create a perfect seal! The disconnect tool also makes it easy to disassemble the pipe and re-use the valves.

The Quadtro Push Connect washing machine box also allows for right, left, or center drain and bottom or top mount valves. Made of high impact polystyrene and supplied with four mounting brackets, the Quadtro boxes provide maximum durability and performance for residential applications.

DRAIN CAN BE INSTALLED LEFT, RIGHT OR CENTER



USE ON COPPER, PEX AND CPVC

THE QUADTRO ADVANTAGE

- > **Flexibility** – Allows for right, left, or center drain and bottom or top mount valves
- > **Easy installation** – “Lock & Load” valve mounting system for quick and easy positioning
- > **Durability** – Box and support brackets made from high-impact polystyrene
- > **Variety** – Boxes are available in various tail piece configurations, giving you the specific product your customers need, including Water Hammer Arrestor SKUs

See reverse side for product and part number information.

Oatey® Quadtro® Washing Machine Outlet Boxes

Part Number	Valve	Tail Piece	No Hammer/ Hammer	Valves Assembled/ Unassembled	Pack Type	Pack Quantity
No Hammer						
38530	1/4 Turn	Copper	No Hammer	Unassembled	Standard	12
38560	1/4 Turn	Copper	No Hammer	Unassembled	Contractor	12
38529	1/4 Turn	Copper	No Hammer	Unassembled	Display	4
38531	1/4 Turn	CPVC	No Hammer	Unassembled	Standard	12
38561	1/4 Turn	CPVC	No Hammer	Unassembled	Contractor	12
38528	1/4 Turn	ASTM F1807	No Hammer	Unassembled	Display	4
38532	1/4 Turn	ASTM F1807	No Hammer	Unassembled	Standard	12
38562	1/4 Turn	ASTM F1807	No Hammer	Unassembled	Contractor	12
38533	1/4 Turn	ASTM F1960	No Hammer	Unassembled	Standard	12
38563	1/4 Turn	ASTM F1960	No Hammer	Unassembled	Contractor	12
38330	1/4 Turn	Viega PEX Press	No Hammer	Unassembled	Standard	12
38338	1/4 Turn	Viega PEX Press	No Hammer	Unassembled	Contractor	12
38300	1/4 Turn	Push Connect	No Hammer	Unassembled	Display	4
38310	1/4 Turn	Push Connect	No Hammer	Unassembled	Standard	12
38318	1/4 Turn	Push Connect	No Hammer	Unassembled	Contractor	12
38535	Single Lever	Copper	No Hammer	Unassembled	Standard	12
38568	Single Lever	Copper	No Hammer	Unassembled	Display	4
38536	Single Lever	CPVC	No Hammer	Unassembled	Standard	12
38537	Single Lever	ASTM F1807	No Hammer	Unassembled	Standard	12
38538	Single Lever	ASTM F1960	No Hammer	Unassembled	Standard	12
38350	Single Lever	Viega PEX Press	No Hammer	Unassembled	Standard	12
38552	Boiler Drain	Copper	No Hammer	Unassembled	Standard	12
38553	Boiler Drain w/ Stop	Copper	No Hammer	Unassembled	Standard	12
38554	North American Boiler Drain	Copper	No Hammer	Unassembled	Standard	12
Hammer						
38540	1/4 Turn	Copper	Hammer	Unassembled	Standard	12
38569	1/4 Turn	Copper	Hammer	Unassembled	Display	2
38541	1/4 Turn	CPVC	Hammer	Unassembled	Standard	12
38542	1/4 Turn	ASTM F1807	Hammer	Unassembled	Standard	12
38543	1/4 Turn	ASTM F1960	Hammer	Unassembled	Standard	12
38331	1/4 Turn	Viega PEX Press	Hammer	Unassembled	Standard	12
38339	1/4 Turn	Viega PEX Press	Hammer	Unassembled	Contractor	12
38301	1/4 Turn	Push Connect	Hammer	Unassembled	Display	4
38311	1/4 Turn	Push Connect	Hammer	Unassembled	Standard	12
38319	1/4 Turn	Push Connect	Hammer	Unassembled	Contractor	12
38545	Single Lever	Copper	Hammer	Unassembled	Standard	12
38546	Single Lever	CPVC	Hammer	Unassembled	Standard	12
38547	Single Lever	ASTM F1807	Hammer	Unassembled	Standard	12
38548	Single Lever	ASTM F1960	Hammer	Unassembled	Standard	12
38351	Single Lever	Viega PEX Press	Hammer	Unassembled	Standard	12
38550	Plain Box	-	-	Unassembled	Standard	12

Accessories

Product Number	Description	Carton Quantity
38550	Plain Box No Valves – Standard Pack with Grommets	12
38460	Quadro Test Cap and Gauge	1
38576	Quadro Test Cap	12
38577	Quadro Hub/O-Ring	24
38941	Quadro Plastic Faceplate	12
38768	Brackets, 4" Long Plastic	12
38648	Brackets, 12" Long Plastic	12



db Dearborn Brass



OATEYSCS



Oatey

Order Today!

Contact your local Oatey sales representative to place your order.

©2016 OateySCS. All Rights Reserved. This information is based on data believed to be reliable but Oatey makes no warranties, express or implied, as to its accuracy and assumes no liability arising out of its use. The data listed falls within the normal range of product properties but should not be used to establish specification limits or used alone as the basis of design. Oatey's liability to purchasers is expressly limited to the terms and conditions of sale. Oatey is a trademark of Oatey Co. All other trademarks can be found on www.oatey.com.